



6Bit Adapter

User Manual


Please read the manual carefully before use and save it for future use.

Function button description

Reset button

Focal length dial

Unlock button



Note (M-Z 6Bit Adapter Ring)

1. The aperture data can be recorded as long as the aperture setting on the camera system is the same as the aperture when you take photos (Aperture \geq F5.6 can be recorded).
2. When using a lens without the 6Bit contact, the focal length dial needs to be set to be consistent with the focal length of the lens. Press the reset button to record the focal length information 28/35/50/75/90/135;
3. Use the lens with the 6Bit contact, there is no need to set the focal length dial. Press the reset button to record the focal length information;
4. Support to automatically turn on the anti-shake function of the camera body (the camera needs to have this function, such as Nikon Z6);
5. Support a trap focus, turn on the autofocus mode of the body, press the shutter fully, and turn the focus ring until the frame is clear, and the photo can be taken automatically;
6. Support focus indication function, which can be displayed when manual focus mode is turned on (the body needs to have this function, such as Nikon Z6);

Note (M-E 6Bit Adapter Ring)

1. The aperture data can be recorded as long as the aperture setting on the camera system is the same as the aperture when you take photos.
2. When using a lens without the 6Bit contact, the focal length dial needs to be set to be consistent with the focal length of the lens. Press the reset button to record the focal length information 28/35/50/75/90/135;
3. Use the lens with the 6Bit contact, there is no need to set the focal length dial. Press the reset button to record the focal length information;
4. Support to automatically turn on the anti-shake function of the camera body (the camera needs to have this function, such as SONY A7M3);
5. THE Exif recording function cannot be reached on the NEX series camera. ;



M-Z 6Bit Instruction Video



M-E 6Bit Instruction Video



Visit the TTArtisan Official Web to view more products
<https://www.ttartisan.com>