

0107 Polarizer/Depolarizer

Z3100-P



980 nm In-line Depolarizer, PM-PM

The depolarizer divides an input beam into two orthogonally polarized beams of equal power. It introduces a delay in one beam before reuniting both using a polarization combiner. The delay exceeds the coherence length of the light source, removing the fixed phase relationship upon recombination.

FEATURES

- Low Insertion Loss
- High Return Loss
- High Extinction Ratio


- High Reliability
- High Stability

USE IN

- Communication Systems
- Test Instrument

- Fiber Sensor
- Research

MECHANICAL DRAWING



980 nm
±10 nm
0.7 dB typ.; 0.9 dB max.
50 dB min.
30 dB max.
300 mW max.
5 N max.
-5°C to +70°C
-40°C to +85°C
PM-PM
5.5x5.5x35 mm

Order notes to our customers: The default parameters are as follows. For special needs, please contact sales.

- 1) Connector FC/APC, 900 um, 1 m by default for all devices except for high power devices.
- 2) Slow axis working, fast axis blocked, connector key is aligned to slow axis by default for PM devices.