SIMÓLIO®

Hearing Protection Stereo Headphones

SM-904





User Manual

Sales & Support Email: support 1@simolio.com (for NA/AU) support_uk@simolio.com (for UK)

Sales & Support Email: support 1@simolio.com (for NA/AU) support_uk@simolio.com (for UK)

SIMOLIO SM-904 Manual

Thank you for choosing SIMOLIO SM-904, which is specifically designed for you to enjoy music and other content in a safe, creative and sustainable way with great sound experience. Please read this guide carefully so you can take full advantage of SIMOLIO and keep it in a safe place for future reference. We hope that you're very happy with your SIMOLIO, if you have any questions, please feel free to contact us via: support1@simolio.com (for NA/AU) support_uk@simolio.com (for UK)
Response Time: 2-24h, excl. holidays

Contents


1. Package Contents	01
2. Product Diagram	01
3. Features	02
4. Using Your Headphones	03
4.1 Adjust the 3-level volume limiter switch (104dB/94dB/85dB)	03
4.2 Basic Operation	04
4.3 Using the Headphones with Your Devices	05
4.4 Use Sharing Port between Two Headphones	06
5. Safety Instructions	07
6. Limited Warranty	08

SIMOLIO SM-904 Manual

1. Package Contents



2. Product Diagram





3. Features

(1) Three Switchable Volume Limited Levels for Hearing Protection To protect vulnerable and sensitive ears. Slide the volume limiter switch to 85dB or 94dB to limit the output volume at the desired sound level.

Note:

* The limit at 104 dB is only a temporary option for noisy situations, like on the train or plane.

(2) Hands-free Talking and In-line Volume Control

The built-in HD microphone and volume control on the cable guarantees clear, hands-free communication, with one multi-function button to control music play and phone calls.

(3) With Sharing Port, No More Audio Splitter is Needed

With a sharing port on the left side of the headphones, you can connect with another headphones to share the video/music with your friends without any splitters needed.

(4) Foldable & Durable Design

The foldable design makes these headphones easy to store and carry for travel or school. The adjustable headband with memory stainless steel strips

give these headphones some impressive flexibility and durability so they can adapt to the shape of user's head and withstand rough play.

(5) Comfortable Wearing

Equipped with soft on-ear cushions to provide premium comfort during long time listening.

4. Using Your Headphones

4.1 Adjust the 3-level volume limiter switch (104dB/94dB/85dB)

Slide the volume limiter switch to limit the headphones' output volume at the desired sound level for teenagers or adults

Volume Limiter Switch	Operation for Hearing Protection		
85dB	For teens,the max output Vol ≤ 85dB		
94dB	For adults, the max output Vol ≤ 94dB		
104dB	The limit at 104 dB is only a temporary option for noisy situations, like on the train or plane.		



4.2 Basic Operation (MFB for smart phones only)

In the in-line audio control cable we have integrated a MFB button and volume slider.

Button	Function	Operation
MFB (Multi-function Button)	Answer a call/End a call	Press MFB once
	Reject a call	Press and hold MFB for 3 seconds
	Play/Pause media	Press MFB once
	Next track	Double-press MFB
	Previous track	Triple-press MFB
	Activate voice recognition apps on your mobile device	Pressing MFB button for more than 3 seconds will activate voice command (e.g.,Siri) when connected to an Android or an Apple device
Volume (MAX-MIN)	Volume up	Slide upward gradually to MAX
	Volume down	Slide downward gradually to MIN

SIMOLIO SM-904 Manual

Note:

- * You may need to open the media player application for initial play back to start.
- * If there is a phone call while you are listening to an audio, the phone call will take precedence over the audio, and after the call, it will automatically return to the previous listening state.
- * Not all devices support this in-line control functionality. By using the 3.5mm Mic Audio Y Splitter Cable (purchase separately), you can connect this headphone to a PC or old version Laptop for use with VOIP applications, such as Skype or chat programs, MSN Messenger, Yahoo, Google Voice etc.



3.5mm Mic Audio Y Splitter Cable

* MFB function is only available in smart phone.

4.3 Using the Headphones with Your Devices

Connect $\overline{3}$.5mm jack on the end of the audio cable to your device. Select a desired volume level by the volume limiter switch. Put on the headphones and adjust the headband to your head size to optimize audio and wearing comfort. (Ref. Fig 3)





4.4 Use Sharing Port between Two Headphones

You can share your content like music with your friend by plugging his headphones into the 3.5mm sharing jack on the left side of your SIMOLIO headphones. (Ref.Fig 4)

Note: The volume limited function is only available for SIMOLIO headphones.



5. Safety Instructions



⚠ WARNING

Protect your hearing

Although SIMOLIO are volume limited, children are not recommended to be exposed to listening for more than 2 hours per time. Extended listening may negatively impact hearing.



Beware of your surroundings

Your headphones significantly dampen external sound. Do not in any case wear your headphones when you are required to pay attention to your surroundings.

⚠ CAUTION

Ensure that the headphones do not become wet, protect them from moisture, heat (e.g. during the summer in cars) and mechanical influences (e.g. severe shocks, pressure and dropping).

6.Limited Warranty

12 months limited warranty: Simolio provides full warranty due to defects in materials and workmanship for a period of 12 months from the original date of purchase. The warranty period is not extended if we repair or replace warranted product.

This warranty is provided at the discretion of Simolio Ltd. And does not cover appearance damage or damage due to acts of nature, accident, misuse, abuse, negligence, commercial use, or modification of or to any part of the product. Accessories and perishable items such as earmuffs are not covered under this warranty.

SIMOLIO SM-904 Manual

Please contact: support1@simolio.com (NA/AU) or support_uk@simolio.com (UK) and provide your order number to register the warranty.