



**BUREAU  
VERITAS**

# Unit Certificate

**Manufacturer / applicant:** Hoymiles Power Electronics Inc.  
No 18 Kangjing Road HangZhou,  
Zhejiang Province  
China

<b>Type of power generation unit:</b>	Grid-tied Photovoltaic Microinverter			
<b>Name of PGU:</b>	HM-800	HM-800T	HM-800SL	HM-700
<b>Active power (nominal power at reference conditions) [VA]:</b>	800	800	800	700
<b>Name of PGU:</b>	HM-700T	HM-700SL	HM-600	HM-600T
<b>Active power (nominal power at reference conditions) [VA]:</b>	700	700	600	600
<b>Name of PGU:</b>	HM-500	HM-500T	--	--
<b>Active power (nominal power at reference conditions) [VA]:</b>	500	500	--	--
<b>Rated voltage:</b>	230V; N; PE			

**Firmware version:** Beginning with V01.01.00

**Connection rule:** VDE-AR-N 4105:2018-11 – Power generation systems connected to the low-voltage distribution network  
Technical minimum requirements for the connection to and parallel operation with low-voltage distribution networks.

**Applicable standards / directives:** DIN VDE V 0124-100 (VDE V 0124-100):2020-06 – Grid integration of power generation systems – low voltage  
Test requirements for power generation units to be connected and operated parallel with the low-voltage distribution networks

**The above stated generation units have been tested and certified according to the test guideline VDE 0124-100. The electrical properties required in the connection rule are satisfied.**

- Verification of permissible system perturbations
- Verification of the symmetry characteristics of three-phase inverter modules
- Verification of the characteristics of the power generation unit on the network
- Verification of P<sub>AV,E</sub> surveillance
- Verification of dynamic network support
- Verification of the possibility to take part in the generation management / network security management

**The certificate contains the following information:**

- Technical specifications of the power generation units, the deployed auxiliary equipment and the software version used.
- Summarized information about the characteristics of the power generation unit (mode of operation)

**Report number:** BMH-ESH-P200410697-2-R2

**Certification scheme:** NSOP-0032-DEU-ZE-V01

**Certificate number:** U22-0344

**Date of issue:** 2022-07-01

**Certification body**

Alf ASSENKAMP



Certification body Bureau Veritas Consumer Products Services Germany GmbH accredited according to DIN EN ISO/IEC 17065  
Testing laboratory accredited according to DIN EN ISO/IEC 17025

A partial representation of the certificate requires the written permission of Bureau Veritas Consumer Products Services Germany GmbH

**BUREAU VERITAS**

Consumer Products Services Germany GmbH

Oehleckerring 40, 22419 Hamburg, Germany  
Tel: +49 40 74041-0

cps-hamburg@de.bureauveritas.com  
www.bureauveritas.de/cps



**E.4 and E.5 Requirements for the test report for power generation units**

Extract from the test report for unit certification  
„Determination of electrical properties“

Nr. BMH-ESH-P200410697-2-R2

## Description of the power generation unit

<b>Manufacturer / applicant:</b>	Hoymiles Power Electronics Inc. No 18 Kangjing Road HangZhou, Zhejiang Province China			
<b>Type of power generation unit:</b>	Grid-tied Photovoltaic Microinverter			
<b>Name of PGU:</b>	HM-800	HM-800T	HM-800SL	HM-700
<b>Active power [VA]:</b>	800	800	800	700
<b>Apparent power [VA]:</b>	800	800	800	700
<b>Rated voltage [V]:</b>	220/230/240V; N; PE	220/230/240V; N; PE	220/230/240V; N; PE	220/230/240V; N; PE
<b>Rated current AC I<sub>r</sub> [A]:</b>	4,0	4,0	4,0	3,5
<b>Initial short-circuit current AC I<sub>k</sub> [A]:</b>	5	5	5	5
<b>Name of PGU:</b>	HM-700T	HM-700SL	HM-600	HM-600T
<b>Active power [VA]:</b>	700	700	600	600
<b>Apparent power [VA]:</b>	700	700	600	600
<b>Rated voltage [V]:</b>	220/230/240V;N;PE	220/230/240V;N;PE	220/230/240V;N;PE	220/230/240V;N;PE
<b>Rated current AC I<sub>r</sub> [A]:</b>	3,5	3,5	3,0	3,0
<b>Initial short-circuit current AC I<sub>k</sub> [A]:</b>	5	5	4	4
<b>Name of PGU:</b>	HM-500	HM-500T	--	--
<b>Active power [VA]:</b>	500	500	--	--
<b>Apparent power [VA]:</b>	500	500	--	--
<b>Rated voltage [V]:</b>	220/230/240V;N;PE	220/230/240V;N;PE	--	--
<b>Rated current AC I<sub>r</sub> [A]:</b>	2,5	2,5	--	--
<b>Initial short-circuit current AC I<sub>k</sub> [A]:</b>	4	4	--	--
<b>Firmware version:</b>	Beginning with V01.01.00			
<b>Measurement period:</b>	2021-04-08 to 2021-04-13			

**Description of the structure of the power generation unit:**

The power generation unit is equipped with a PV and line-side EMC filter. The power generation unit has galvanic isolation between DC input and AC output (transformer). Output switch-off is performed with single-fault tolerance due to the inverter bridge and one relay. This enables a safe disconnection of the power generation unit from the network in case of error.



**E.4 and E.5 Requirements for the test report for power generation units**

**Extract from the test report for unit certification  
„Determination of electrical properties“**

**Nr. BMH-ESH-P200410697-2-R2**

**5.4.2 Active- / Apparent power**

(results at nominal grid voltage)

Name of PGU:	HM-800	HM-700	HM-600	HM-500
$P_{E_{max}}$ [kW] at $\cos \varphi = 1$	796,69	705,32	607,65	503,43
$S_{E_{max}}$ [kVA] at $\cos \varphi = 1$	796,81	706,04	607,78	503,59
$P_{E_{max}}$ [kW] at $\cos \varphi$ under-excite = 0,9	721,11	631,11	547,98	455,58
$S_{E_{max}}$ [kVA] at $\cos \varphi$ under-excite = 0,9	800,54	702,21	607,98	506,08
$P_{E_{max}}$ [kW] at $\cos \varphi$ over-excited = 0,9	722,58	632,11	548,92	459,56
$S_{E_{max}}$ [kVA] at $\cos \varphi$ over-excited = 0,9	803,64	701,43	609,51	510,54

Note:

For the implementation of a reactive power set point assignment, the active power is reduced if necessary.

**5.4.8 Reactive power supply**

(results at nominal grid voltage)

Name of PGU:	HM-800	
Active power	40 – 60 % $P_{E_{max}}$	$S_{E_{max}}$
$\cos \varphi$ under-excite:	0,9546	0,9526
$\cos \varphi$ over-excited	0,9493	0,9518
$\cos \varphi$ setpoint	0,950	0,950
$\cos \varphi$ under-excite:	0,9825	0,9818
$\cos \varphi$ over-excited	0,9810	0,9802
$\cos \varphi$ setpoint	0,980	0,980

**5.4.8.3 Reactive power transfer function – standard  $\cos \varphi$  (P)-characteristic curve**

Name of PGU:	HM-800									
Active power $P_{E_{max}}$ setpoint [%]	10	20	30	40	50	60	70	80	90	100
Active power $P_{E_{max}}$ [%]	--	19,08	29,84	40,15	49,86	60,46	70,83	81,12	91,18	101,34
$\cos \varphi$ setpoint of $P_{E_{max}}$	--	1,0000	1,0000	1,0000	1,0000	0,9800	0,9600	0,9400	0,9200	0,9000
$\cos \varphi$ measured	--	0,9925	0,9940	0,9955	0,9968	0,9808	0,9658	0,9445	0,9257	0,9039

According to VDE 0124-100, an accuracy of  $\cos \varphi$  0,01 is required for testing the Reactive power transfer function. The standard  $\cos \varphi$ -(P)-characteristic curve is respected. To provide the set point of the reactive power, active power will be reduced at 100 %  $P / P_n$ .



**E.4 and E.5 Requirements for the test report for power generation units**

**Extract from the test report for unit certification  
„Determination of electrical properties“**

**Nr. BMH-ESH-P200410697-2-R2**

**5.2.2 Switching operations**

HM-800		L1	L2	L3
Switch-on without specification (to the primary energy source)	$k_i$	0,07	--	--
Unfavorable case when switching the generator step	$k_i$	N/A	N/A	N/A
Switch-on at auxiliary conditions (of the primary energy source)	$k_i$	0,13	--	--
Switch-off at auxiliary conditions (of the primary energy source)	$k_i$	0,65	--	--
Worst value of all switching operations	$k_i$	0,65	--	--
HM-700		L1	L2	L3
Switch-on without specification (to the primary energy source)	$k_i$	0,07	--	--
Unfavorable case when switching the generator step	$k_i$	N/A	N/A	N/A
Switch-on at auxiliary conditions (of the primary energy source)	$k_i$	0,30	--	--
Switch-off at auxiliary conditions (of the primary energy source)	$k_i$	0,89	--	--
Worst value of all switching operations	$k_i$	0,89	--	--
HM-600		L1	L2	L3
Switch-on without specification (to the primary energy source)	$k_i$	0,09	--	--
Unfavorable case when switching the generator step	$k_i$	N/A	N/A	N/A
Switch-on at auxiliary conditions (of the primary energy source)	$k_i$	0,32	--	--
Switch-off at auxiliary conditions (of the primary energy source)	$k_i$	0,91	--	--
Worst value of all switching operations	$k_i$	0,91	--	--
HM-500		L1	L2	L3
Switch-on without specification (to the primary energy source)	$k_i$	0,10	--	--
Unfavorable case when switching the generator step	$k_i$	N/A	N/A	N/A
Switch-on at auxiliary conditions (of the primary energy source)	$k_i$	0,31	--	--
Switch-off at auxiliary conditions (of the primary energy source)	$k_i$	0,91	--	--
Worst value of all switching operations	$k_i$	0,91	--	--

**5.2.3 Flicker for rated current  $\leq 75A$  according to DIN EN 61000-3-3 (VDE 0838-3)**

Impedance:	$R_A = 0,24\Omega$ $jX_A = 0,15\Omega$ $R_N = 0,16\Omega$ $jX_N = 0,10\Omega$
Line impedance angle $\psi_k$	32°
System flicker coefficient $c_{\psi}$	9,87
Short-time flicker $P_{st}$	0,07

**5.2.4.1 a) Harmonics**

The self-generation unit HM-800 is comply with DIN EN 61000-3-2 (VDE 0838-2).



**E.4 and E.5 Requirements for the test report for power generation units**

**Extract from the test report for unit certification  
„Determination of electrical properties“**

**Nr. BMH-ESH-P200410697-2-R2**

**5.2.5.1 b) Harmonics (HM-800)**

P/P <sub>n</sub> [%]	0	10	20	30	40	50	60	70	80	90	100
Order	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]
1	0,927	10,015	20,098	30,318	40,197	50,394	60,306	70,363	80,100	90,007	99,621
2	0,008	0,013	0,013	0,016	0,020	0,029	0,032	0,032	0,033	0,035	0,034
3	0,008	0,299	0,730	0,739	0,715	0,410	0,276	0,278	0,266	0,175	0,128
4	0,008	0,009	0,013	0,014	0,018	0,017	0,018	0,019	0,021	0,022	0,026
5	0,007	0,185	0,428	0,461	0,455	0,572	0,464	0,388	0,411	0,440	0,516
6	0,007	0,011	0,012	0,014	0,014	0,016	0,017	0,015	0,016	0,017	0,020
7	0,008	0,084	0,147	0,171	0,223	0,258	0,411	0,425	0,375	0,311	0,344
8	0,008	0,011	0,011	0,014	0,013	0,015	0,017	0,014	0,016	0,016	0,019
9	0,008	0,059	0,136	0,104	0,102	0,200	0,058	0,221	0,335	0,357	0,329
10	0,008	0,009	0,010	0,013	0,013	0,014	0,016	0,014	0,016	0,017	0,019
11	0,008	0,078	0,197	0,145	0,137	0,115	0,219	0,138	0,053	0,219	0,286
12	0,008	0,010	0,011	0,014	0,014	0,015	0,016	0,017	0,019	0,017	0,019
13	0,008	0,068	0,143	0,140	0,120	0,062	0,083	0,222	0,207	0,080	0,106
14	0,008	0,010	0,011	0,013	0,014	0,015	0,016	0,019	0,018	0,018	0,019
15	0,007	0,044	0,095	0,099	0,078	0,107	0,104	0,055	0,153	0,201	0,159
16	0,008	0,011	0,011	0,014	0,014	0,016	0,016	0,014	0,018	0,018	0,020
17	0,008	0,037	0,093	0,061	0,017	0,110	0,039	0,133	0,086	0,083	0,177
18	0,008	0,010	0,011	0,014	0,015	0,017	0,015	0,015	0,018	0,017	0,021
19	0,008	0,037	0,101	0,046	0,017	0,089	0,093	0,054	0,194	0,151	0,044
20	0,008	0,012	0,012	0,015	0,014	0,016	0,015	0,018	0,018	0,019	0,019
21	0,007	0,030	0,028	0,026	0,033	0,049	0,105	0,055	0,098	0,268	0,249
22	0,008	0,011	0,012	0,013	0,014	0,016	0,015	0,015	0,018	0,018	0,018
23	0,008	0,012	0,024	0,030	0,033	0,100	0,191	0,110	0,055	0,200	0,336
24	0,008	0,010	0,011	0,012	0,014	0,017	0,014	0,013	0,016	0,018	0,018
25	0,008	0,016	0,046	0,056	0,074	0,104	0,091	0,218	0,156	0,081	0,258
26	0,008	0,010	0,010	0,013	0,014	0,013	0,014	0,014	0,016	0,018	0,017
27	0,008	0,021	0,076	0,081	0,110	0,051	0,152	0,173	0,273	0,140	0,142
28	0,008	0,011	0,011	0,013	0,013	0,014	0,014	0,017	0,016	0,018	0,016
29	0,008	0,031	0,062	0,088	0,118	0,187	0,192	0,163	0,270	0,282	0,172
30	0,008	0,010	0,011	0,013	0,013	0,015	0,014	0,016	0,016	0,016	0,016
31	0,008	0,033	0,076	0,101	0,117	0,193	0,151	0,255	0,202	0,362	0,300
32	0,008	0,010	0,011	0,013	0,014	0,014	0,013	0,013	0,015	0,016	0,015
33	0,008	0,035	0,095	0,122	0,144	0,122	0,177	0,245	0,273	0,305	0,390
34	0,008	0,011	0,011	0,013	0,013	0,012	0,015	0,013	0,014	0,015	0,016
35	0,008	0,040	0,115	0,142	0,158	0,194	0,259	0,192	0,303	0,242	0,368
36	0,008	0,010	0,011	0,013	0,013	0,015	0,015	0,015	0,015	0,015	0,015
37	0,008	0,047	0,112	0,139	0,160	0,172	0,195	0,237	0,251	0,295	0,294
38	0,008	0,010	0,011	0,013	0,014	0,014	0,015	0,015	0,015	0,015	0,016
39	0,008	0,051	0,107	0,135	0,159	0,160	0,140	0,314	0,209	0,327	0,300
40	0,008	0,010	0,011	0,014	0,014	0,015	0,014	0,016	0,016	0,016	0,017



**E.4 and E.5 Requirements for the test report for power generation units**

**Extract from the test report for unit certification  
„Determination of electrical properties“**

**Nr. BMH-ESH-P200410697-2-R2**

**5.2.5.1 b) Inter-harmonics (HM-800)**

P/Pn [%]	5	10	20	30	40	50	60	70	80	90	100
f [Hz]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]
75	0,007	0,054	0,073	0,014	0,055	0,058	0,053	0,126	0,065	0,095	0,055
125	0,006	0,006	0,016	0,016	0,006	0,021	0,011	0,010	0,042	0,024	0,068
175	0,004	0,032	0,015	0,008	0,021	0,007	0,017	0,045	0,020	0,061	0,023
225	0,004	0,005	0,022	0,012	0,012	0,014	0,001	0,018	0,021	0,012	0,081
275	0,004	0,009	0,016	0,006	0,013	0,012	0,010	0,023	0,015	0,053	0,046
325	0,007	0,024	0,003	0,006	0,015	0,004	0,001	0,016	0,006	0,026	0,047
375	0,007	0,011	0,019	0,007	0,016	0,014	0,011	0,012	0,010	0,048	0,027
425	0,011	0,031	0,019	0,004	0,009	0,006	0,012	0,025	0,009	0,016	0,026
475	0,010	0,022	0,015	0,007	0,019	0,006	0,013	0,008	0,001	0,044	0,024
525	0,002	0,016	0,008	0,008	0,020	0,007	0,009	0,014	0,004	0,014	0,033
575	0,009	0,015	0,011	0,002	0,014	0,002	0,003	0,006	0,009	0,038	0,036
625	0,006	0,004	0,011	0,010	0,017	0,008	0,008	0,003	0,006	0,016	0,044
675	0,005	0,011	0,018	0,002	0,013	0,010	0,012	0,002	0,012	0,032	0,043
725	0,004	0,017	0,012	0,001	0,006	0,007	0,013	0,002	0,012	0,010	0,013
775	0,012	0,012	0,002	0,003	0,018	0,011	0,018	0,011	0,008	0,027	0,047
825	0,007	0,012	0,012	0,002	0,017	0,008	0,014	0,009	0,023	0,003	0,004
875	0,007	0,009	0,020	0,002	0,017	0,007	0,014	0,009	0,015	0,037	0,020
925	0,009	0,011	0,019	0,003	0,012	0,004	0,018	0,016	0,032	0,021	0,037
975	0,009	0,011	0,002	0,005	0,011	0,006	0,011	0,007	0,004	0,036	0,021
1025	0,006	0,002	0,009	0,008	0,011	0,005	0,007	0,007	0,018	0,015	0,029
1075	0,003	0,026	0,018	0,006	0,013	0,016	0,011	0,007	0,015	0,026	0,007
1125	0,006	0,004	0,016	0,006	0,008	0,011	0,003	0,017	0,010	0,014	0,026
1175	0,007	0,026	0,010	0,003	0,018	0,002	0,017	0,012	0,014	0,008	0,013
1225	0,004	0,014	0,016	0,006	0,010	0,004	0,004	0,014	0,011	0,026	0,037
1275	0,005	0,013	0,020	0,006	0,025	0,002	0,015	0,005	0,018	0,003	0,023
1325	0,003	0,012	0,019	0,010	0,011	0,007	0,007	0,007	0,010	0,032	0,056
1375	0,005	0,014	0,009	0,010	0,008	0,006	0,009	0,004	0,008	0,018	0,032
1425	0,001	0,008	0,011	0,010	0,022	0,006	0,004	0,017	0,010	0,042	0,062
1475	0,006	0,007	0,018	0,001	0,018	0,013	0,017	0,003	0,006	0,006	0,033
1525	0,011	0,009	0,019	0,009	0,011	0,002	0,008	0,016	0,001	0,049	0,039
1575	0,004	0,007	0,013	0,005	0,017	0,007	0,028	0,018	0,012	0,016	0,014
1625	0,012	0,021	0,013	0,010	0,019	0,014	0,013	0,025	0,008	0,034	0,047
1675	0,005	0,015	0,007	0,005	0,011	0,012	0,018	0,028	0,012	0,025	0,030
1725	0,010	0,021	0,022	0,005	0,014	0,013	0,010	0,009	0,010	0,017	0,074
1775	0,007	0,013	0,020	0,005	0,012	0,007	0,005	0,010	0,006	0,037	0,062
1825	0,013	0,016	0,004	0,011	0,017	0,022	0,009	0,012	0,008	0,010	0,091
1875	0,005	0,010	0,010	0,010	0,022	0,012	0,019	0,021	0,005	0,028	0,076
1925	0,003	0,010	0,016	0,017	0,020	0,013	0,011	0,014	0,014	0,021	0,070
1975	0,007	0,010	0,017	0,003	0,009	0,007	0,016	0,007	0,007	0,015	0,065



E.4 and E.5 Requirements for the test report for power generation units

Extract from the test report for unit certification Nr. BMH-ESH-P200410697-2-R2 „Determination of electrical properties“

Table with 12 columns: P/Pn [%], 5, 10, 20, 30, 40, 50, 60, 70, 80, 90, 100. Rows represent frequencies f [kHz] from 2.1 to 8.9. Each cell contains a value for Ih [%].

Note: The reference current is 3,48 A.





E.4 and E.5 Requirements for the test report for power generation units

Extract from the test report for unit certification  
„Determination of electrical properties“

Nr. BMH-ESH-P200410697-2-R2

5.2.5.1 b) Harmonics (HM-700)

P/P <sub>n</sub> [%]	5	10	20	30	40	50	60	70	80	90	100
Order	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]
1	1,055	9,847	18,869	30,455	40,802	50,826	61,161	71,093	81,317	91,208	101,331
2	0,009	0,013	0,015	0,021	0,022	0,027	0,028	0,031	0,028	0,034	0,036
3	0,010	0,386	0,724	0,886	0,872	0,755	0,423	0,343	0,310	0,309	0,228
4	0,009	0,010	0,014	0,018	0,020	0,020	0,018	0,022	0,024	0,025	0,023
5	0,009	0,136	0,270	0,520	0,540	0,573	0,664	0,544	0,447	0,464	0,491
6	0,009	0,013	0,013	0,015	0,015	0,019	0,018	0,017	0,017	0,020	0,018
7	0,009	0,084	0,135	0,159	0,210	0,207	0,388	0,499	0,496	0,443	0,377
8	0,009	0,011	0,012	0,015	0,015	0,016	0,016	0,018	0,017	0,019	0,018
9	0,009	0,127	0,209	0,129	0,125	0,238	0,190	0,097	0,273	0,383	0,415
10	0,009	0,012	0,012	0,015	0,015	0,015	0,016	0,017	0,017	0,020	0,019
11	0,009	0,082	0,193	0,209	0,172	0,143	0,194	0,271	0,146	0,051	0,217
12	0,009	0,012	0,012	0,015	0,015	0,016	0,016	0,017	0,019	0,022	0,020
13	0,009	0,051	0,094	0,163	0,140	0,142	0,073	0,147	0,260	0,248	0,122
14	0,009	0,013	0,012	0,015	0,015	0,017	0,017	0,020	0,021	0,022	0,020
15	0,009	0,051	0,087	0,097	0,063	0,119	0,078	0,102	0,064	0,169	0,241
16	0,009	0,013	0,012	0,015	0,015	0,018	0,015	0,021	0,019	0,021	0,018
17	0,009	0,058	0,101	0,071	0,036	0,103	0,151	0,046	0,147	0,102	0,077
18	0,009	0,012	0,012	0,015	0,016	0,018	0,017	0,018	0,018	0,021	0,018
19	0,009	0,029	0,064	0,091	0,054	0,035	0,093	0,121	0,073	0,207	0,187
20	0,009	0,012	0,011	0,015	0,014	0,017	0,016	0,016	0,019	0,021	0,020
21	0,009	0,023	0,027	0,030	0,018	0,137	0,159	0,095	0,056	0,090	0,283
22	0,009	0,011	0,011	0,015	0,013	0,016	0,015	0,016	0,016	0,019	0,020
23	0,009	0,030	0,039	0,047	0,054	0,115	0,029	0,211	0,107	0,068	0,175
24	0,009	0,012	0,011	0,014	0,014	0,016	0,016	0,016	0,015	0,019	0,019
25	0,009	0,017	0,050	0,048	0,077	0,056	0,142	0,127	0,239	0,176	0,063
26	0,009	0,012	0,011	0,015	0,014	0,016	0,015	0,016	0,017	0,018	0,017
27	0,009	0,024	0,043	0,089	0,101	0,155	0,123	0,154	0,212	0,304	0,178
28	0,009	0,011	0,011	0,014	0,013	0,016	0,014	0,017	0,018	0,017	0,018
29	0,009	0,032	0,062	0,082	0,112	0,249	0,108	0,232	0,166	0,284	0,338
30	0,009	0,013	0,012	0,015	0,014	0,016	0,014	0,017	0,018	0,018	0,018
31	0,009	0,037	0,072	0,107	0,119	0,138	0,259	0,190	0,276	0,218	0,390
32	0,009	0,011	0,012	0,015	0,014	0,015	0,014	0,015	0,016	0,018	0,018
33	0,009	0,042	0,087	0,127	0,132	0,053	0,212	0,164	0,280	0,312	0,292
34	0,009	0,012	0,012	0,014	0,014	0,016	0,014	0,016	0,016	0,017	0,017
35	0,009	0,049	0,092	0,145	0,162	0,255	0,138	0,291	0,222	0,329	0,266
36	0,009	0,012	0,011	0,015	0,014	0,016	0,014	0,016	0,017	0,018	0,016
37	0,009	0,051	0,097	0,137	0,183	0,209	0,233	0,272	0,244	0,256	0,345
38	0,009	0,011	0,011	0,014	0,014	0,016	0,016	0,017	0,018	0,019	0,017
39	0,009	0,054	0,104	0,140	0,181	0,207	0,220	0,161	0,350	0,231	0,362
40	0,009	0,011	0,012	0,015	0,014	0,016	0,015	0,017	0,018	0,020	0,018





E.4 and E.5 Requirements for the test report for power generation units

Extract from the test report for unit certification Nr. BMH-ESH-P200410697-2-R2 „Determination of electrical properties“

5.2.5.1 b) Inter-harmonics (HM-700)

Table with 12 columns: P/Pn [%], 5, 10, 20, 30, 40, 50, 60, 70, 80, 90, 100. Rows include f [Hz] and Ih [%] for various frequencies from 75 to 1975 Hz.



**E.4 and E.5 Requirements for the test report for power generation units**

**Extract from the test report for unit certification  
„Determination of electrical properties“**

**Nr. BMH-ESH-P200410697-2-R2**

**5.2.5.1 b) Higher frequencies (HM-700)**

P/P <sub>n</sub> [%]	5	10	20	30	40	50	60	70	80	90	100
f [kHz]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]
2,1	0,43	0,42	0,45	0,48	0,44	0,46	0,44	0,43	0,45	0,47	0,42
2,3	0,40	0,39	0,40	0,42	0,40	0,39	0,39	0,36	0,38	0,39	0,38
2,5	0,40	0,42	0,39	0,37	0,39	0,40	0,42	0,44	0,41	0,37	0,40
2,7	0,42	0,41	0,43	0,44	0,44	0,42	0,41	0,38	0,40	0,39	0,39
2,9	0,36	0,36	0,36	0,36	0,37	0,36	0,35	0,36	0,35	0,37	0,35
3,1	0,37	0,38	0,36	0,35	0,37	0,36	0,36	0,36	0,35	0,35	0,36
3,3	0,35	0,34	0,35	0,36	0,35	0,35	0,35	0,34	0,34	0,34	0,34
3,5	0,35	0,35	0,36	0,36	0,36	0,36	0,35	0,35	0,36	0,37	0,36
3,7	0,34	0,34	0,34	0,34	0,34	0,34	0,34	0,34	0,34	0,34	0,34
3,9	0,33	0,33	0,34	0,34	0,33	0,34	0,33	0,33	0,34	0,33	0,34
4,1	0,34	0,34	0,34	0,34	0,34	0,34	0,34	0,34	0,34	0,34	0,34
4,3	0,33	0,33	0,33	0,33	0,33	0,33	0,33	0,33	0,33	0,33	0,33
4,5	0,33	0,33	0,33	0,33	0,33	0,33	0,33	0,33	0,33	0,33	0,33
4,7	0,33	0,34	0,33	0,34	0,34	0,33	0,34	0,33	0,33	0,33	0,33
4,9	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32
5,1	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32
5,3	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32
5,5	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32
5,7	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32	0,32
5,9	0,31	0,32	0,32	0,32	0,31	0,32	0,31	0,31	0,32	0,31	0,32
6,1	0,31	0,31	0,31	0,31	0,31	0,31	0,32	0,31	0,31	0,31	0,31
6,3	0,31	0,31	0,31	0,32	0,31	0,31	0,31	0,31	0,31	0,31	0,31
6,5	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31
6,7	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31
6,9	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31
7,1	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31
7,3	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31
7,5	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,30	0,31
7,7	0,30	0,30	0,30	0,31	0,31	0,31	0,30	0,31	0,31	0,30	0,30
7,9	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,31	0,30
8,1	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,31
8,3	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30
8,5	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30
8,7	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30
8,9	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30	0,30

Note:  
The reference current is 3,04 A.



E.4 and E.5 Requirements for the test report for power generation units

Extract from the test report for unit certification Nr. BMH-ESH-P200410697-2-R2 „Determination of electrical properties“

5.2.5.1 b) Harmonics (HM-600)

Table with 12 columns: P/Pn [%], 5, 10, 20, 30, 40, 50, 60, 70, 80, 90, 100. Rows include Order, Ih [%], and harmonic orders 1 through 40.



**E.4 and E.5 Requirements for the test report for power generation units**

**Extract from the test report for unit certification  
„Determination of electrical properties“**

**Nr. BMH-ESH-P200410697-2-R2**

**5.2.5.1 b) Inter-harmonics (HM-600)**

P/Pn [%]	5	10	20	30	40	50	60	70	80	90	100
f [Hz]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]
75	2,110	0,027	0,017	0,036	0,010	0,129	0,075	0,121	0,067	0,134	0,224
125	0,577	0,019	0,021	0,013	0,014	0,072	0,025	0,045	0,013	0,103	0,126
175	0,185	0,006	0,018	0,015	0,033	0,027	0,018	0,022	0,009	0,035	0,060
225	0,196	0,006	0,011	0,012	0,007	0,028	0,032	0,020	0,009	0,026	0,063
275	0,045	0,011	0,017	0,010	0,019	0,020	0,015	0,015	0,007	0,024	0,050
325	0,020	0,017	0,008	0,024	0,008	0,009	0,020	0,009	0,028	0,036	0,030
375	0,043	0,009	0,020	0,012	0,006	0,032	0,026	0,010	0,012	0,037	0,038
425	0,026	0,003	0,005	0,006	0,008	0,031	0,002	0,012	0,015	0,045	0,032
475	0,091	0,009	0,011	0,010	0,013	0,016	0,026	0,013	0,004	0,008	0,060
525	0,047	0,015	0,010	0,003	0,008	0,019	0,008	0,013	0,002	0,017	0,037
575	0,020	0,007	0,006	0,002	0,018	0,030	0,015	0,007	0,008	0,026	0,067
625	0,031	0,008	0,016	0,013	0,011	0,031	0,002	0,015	0,001	0,020	0,049
675	0,034	0,010	0,006	0,017	0,007	0,016	0,012	0,014	0,017	0,037	0,056
725	0,003	0,015	0,012	0,011	0,008	0,011	0,013	0,009	0,016	0,021	0,024
775	0,036	0,016	0,005	0,005	0,018	0,018	0,016	0,002	0,013	0,026	0,044
825	0,009	0,009	0,013	0,011	0,011	0,034	0,017	0,012	0,008	0,018	0,018
875	0,035	0,013	0,011	0,014	0,002	0,005	0,021	0,005	0,011	0,038	0,027
925	0,024	0,030	0,011	0,015	0,005	0,011	0,014	0,013	0,006	0,039	0,035
975	0,018	0,008	0,008	0,010	0,023	0,011	0,008	0,017	0,012	0,039	0,044
1025	0,016	0,019	0,012	0,008	0,008	0,018	0,007	0,022	0,019	0,032	0,050
1075	0,023	0,005	0,015	0,014	0,008	0,012	0,002	0,008	0,011	0,032	0,053
1125	0,016	0,032	0,005	0,018	0,004	0,018	0,007	0,020	0,011	0,017	0,044
1175	0,031	0,012	0,009	0,012	0,014	0,017	0,019	0,004	0,014	0,041	0,049
1225	0,023	0,019	0,011	0,013	0,013	0,014	0,011	0,011	0,003	0,020	0,037
1275	0,024	0,004	0,020	0,014	0,005	0,005	0,008	0,003	0,014	0,036	0,030
1325	0,007	0,032	0,009	0,012	0,007	0,021	0,012	0,006	0,008	0,035	0,037
1375	0,014	0,005	0,008	0,016	0,009	0,021	0,009	0,010	0,007	0,029	0,020
1425	0,016	0,017	0,008	0,016	0,003	0,031	0,014	0,012	0,012	0,027	0,029
1475	0,018	0,006	0,007	0,020	0,012	0,007	0,026	0,029	0,004	0,026	0,025
1525	0,036	0,018	0,009	0,007	0,010	0,007	0,023	0,017	0,002	0,032	0,044
1575	0,025	0,017	0,010	0,006	0,013	0,030	0,017	0,011	0,020	0,027	0,023
1625	0,021	0,013	0,014	0,021	0,009	0,018	0,008	0,011	0,010	0,039	0,043
1675	0,010	0,002	0,007	0,017	0,007	0,030	0,012	0,007	0,003	0,030	0,042
1725	0,015	0,012	0,019	0,013	0,002	0,011	0,009	0,007	0,002	0,030	0,037
1775	0,014	0,013	0,006	0,011	0,012	0,028	0,019	0,020	0,013	0,026	0,026
1825	0,012	0,020	0,011	0,011	0,005	0,011	0,005	0,010	0,012	0,019	0,042
1875	0,006	0,007	0,010	0,003	0,017	0,021	0,011	0,018	0,009	0,006	0,028
1925	0,017	0,013	0,006	0,009	0,012	0,031	0,018	0,013	0,015	0,017	0,035
1975	0,013	0,008	0,007	0,004	0,005	0,016	0,013	0,010	0,007	0,013	0,033



E.4 and E.5 Requirements for the test report for power generation units

Extract from the test report for unit certification Nr. BMH-ESH-P200410697-2-R2 „Determination of electrical properties“

Table with 12 columns: P/Pn [%], 5, 10, 20, 30, 40, 50, 60, 70, 80, 90, 100. Rows represent frequencies from 2.1 to 8.9 kHz and corresponding Ih [%] values.

Note: The reference current is 2,61 A.



E.4 and E.5 Requirements for the test report for power generation units

Extract from the test report for unit certification  
„Determination of electrical properties“

Nr. BMH-ESH-P200410697-2-R2

5.2.5.1 b) Harmonics (HM-500)

P/P <sub>n</sub> [%]	5	10	20	30	40	50	60	70	80	90	100
Order	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]
1	1,473	9,751	18,436	29,027	40,273	50,212	60,420	70,307	80,557	90,442	100,658
2	0,013	0,079	0,024	0,025	0,028	0,030	0,033	0,039	0,040	0,037	0,036
3	0,014	0,303	0,559	1,100	1,221	1,202	1,177	1,039	0,675	0,533	0,482
4	0,013	0,025	0,017	0,018	0,020	0,024	0,025	0,027	0,027	0,026	0,024
5	0,012	0,186	0,354	0,517	0,709	0,756	0,747	0,773	0,937	0,874	0,750
6	0,013	0,023	0,017	0,018	0,019	0,021	0,022	0,026	0,027	0,025	0,022
7	0,013	0,135	0,270	0,216	0,240	0,279	0,321	0,288	0,428	0,620	0,703
8	0,012	0,019	0,016	0,017	0,018	0,020	0,020	0,023	0,024	0,022	0,021
9	0,013	0,108	0,193	0,278	0,209	0,168	0,173	0,334	0,324	0,172	0,156
10	0,013	0,018	0,016	0,016	0,018	0,021	0,020	0,021	0,022	0,022	0,022
11	0,013	0,120	0,198	0,290	0,298	0,228	0,242	0,214	0,178	0,357	0,375
12	0,013	0,017	0,016	0,016	0,017	0,021	0,020	0,023	0,023	0,023	0,022
13	0,013	0,112	0,222	0,159	0,221	0,220	0,211	0,184	0,107	0,072	0,222
14	0,013	0,016	0,016	0,017	0,018	0,021	0,020	0,024	0,024	0,024	0,022
15	0,012	0,077	0,177	0,133	0,162	0,158	0,086	0,153	0,179	0,123	0,136
16	0,013	0,016	0,016	0,016	0,017	0,020	0,021	0,025	0,023	0,022	0,022
17	0,013	0,056	0,100	0,167	0,128	0,096	0,023	0,157	0,169	0,176	0,078
18	0,012	0,016	0,016	0,016	0,017	0,020	0,021	0,024	0,024	0,021	0,021
19	0,012	0,048	0,063	0,107	0,138	0,062	0,048	0,048	0,142	0,155	0,168
20	0,013	0,015	0,016	0,016	0,018	0,020	0,020	0,024	0,023	0,022	0,019
21	0,012	0,041	0,068	0,035	0,046	0,042	0,059	0,161	0,074	0,226	0,121
22	0,012	0,015	0,015	0,015	0,018	0,019	0,019	0,023	0,025	0,021	0,020
23	0,012	0,033	0,078	0,056	0,038	0,053	0,057	0,184	0,162	0,171	0,290
24	0,012	0,015	0,014	0,015	0,016	0,019	0,018	0,022	0,023	0,021	0,019
25	0,013	0,027	0,061	0,076	0,073	0,092	0,123	0,076	0,153	0,138	0,212
26	0,012	0,015	0,015	0,016	0,017	0,018	0,020	0,022	0,021	0,023	0,020
27	0,012	0,030	0,052	0,057	0,145	0,127	0,147	0,197	0,074	0,235	0,198
28	0,012	0,014	0,015	0,016	0,017	0,020	0,018	0,023	0,021	0,020	0,020
29	0,012	0,035	0,066	0,081	0,111	0,137	0,161	0,363	0,302	0,184	0,331
30	0,012	0,014	0,015	0,016	0,017	0,020	0,018	0,022	0,022	0,020	0,020
31	0,012	0,040	0,080	0,114	0,123	0,163	0,183	0,149	0,296	0,221	0,288
32	0,012	0,015	0,015	0,016	0,017	0,019	0,019	0,022	0,020	0,022	0,019
33	0,012	0,045	0,092	0,130	0,180	0,203	0,210	0,115	0,182	0,376	0,225
34	0,012	0,015	0,015	0,016	0,017	0,020	0,019	0,024	0,021	0,021	0,019
35	0,013	0,052	0,101	0,148	0,223	0,235	0,231	0,359	0,310	0,286	0,393
36	0,012	0,014	0,016	0,017	0,018	0,021	0,020	0,022	0,023	0,021	0,021
37	0,012	0,055	0,107	0,165	0,183	0,213	0,244	0,298	0,256	0,227	0,413
38	0,012	0,014	0,015	0,016	0,017	0,020	0,019	0,023	0,021	0,021	0,021
39	0,013	0,061	0,114	0,171	0,171	0,208	0,255	0,275	0,253	0,357	0,252
40	0,012	0,015	0,016	0,017	0,018	0,020	0,019	0,023	0,022	0,022	0,021



E.4 and E.5 Requirements for the test report for power generation units

Extract from the test report for unit certification  
„Determination of electrical properties“

Nr. BMH-ESH-P200410697-2-R2

5.2.5.1 b) Inter-harmonics HM-500)

P/Pn [%]	5	10	20	30	40	50	60	70	80	90	100
f [Hz]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]
75	0,001	0,073	0,001	0,047	0,118	0,035	0,048	0,030	0,169	0,109	0,055
125	0,000	0,035	0,005	0,008	0,016	0,014	0,009	0,010	0,046	0,032	0,045
175	0,000	0,006	0,011	0,006	0,036	0,018	0,037	0,018	0,034	0,036	0,044
225	0,000	0,003	0,005	0,010	0,034	0,010	0,021	0,017	0,014	0,037	0,013
275	0,000	0,006	0,010	0,006	0,003	0,017	0,033	0,009	0,022	0,009	0,037
325	0,000	0,003	0,004	0,019	0,016	0,019	0,025	0,014	0,021	0,029	0,018
375	0,000	0,005	0,007	0,007	0,001	0,012	0,014	0,012	0,003	0,017	0,010
425	0,000	0,009	0,010	0,013	0,001	0,019	0,028	0,018	0,026	0,006	0,011
475	0,000	0,006	0,011	0,004	0,028	0,011	0,019	0,011	0,015	0,016	0,009
525	0,000	0,016	0,004	0,009	0,018	0,018	0,007	0,024	0,028	0,013	0,017
575	0,000	0,012	0,005	0,009	0,011	0,007	0,015	0,008	0,026	0,014	0,019
625	0,000	0,003	0,000	0,011	0,007	0,022	0,031	0,014	0,035	0,008	0,027
675	0,000	0,019	0,002	0,013	0,011	0,007	0,013	0,005	0,028	0,012	0,016
725	0,000	0,017	0,006	0,007	0,008	0,004	0,019	0,003	0,023	0,018	0,026
775	0,001	0,007	0,012	0,008	0,012	0,024	0,011	0,025	0,031	0,006	0,017
825	0,000	0,015	0,003	0,004	0,025	0,027	0,031	0,020	0,015	0,006	0,026
875	0,001	0,015	0,004	0,007	0,009	0,019	0,012	0,011	0,023	0,017	0,031
925	0,001	0,007	0,004	0,013	0,035	0,015	0,011	0,025	0,006	0,006	0,025
975	0,001	0,010	0,014	0,004	0,020	0,019	0,020	0,009	0,020	0,005	0,024
1025	0,001	0,012	0,004	0,006	0,027	0,003	0,014	0,035	0,009	0,015	0,024
1075	0,000	0,007	0,004	0,006	0,010	0,015	0,015	0,024	0,027	0,018	0,005
1125	0,000	0,015	0,002	0,007	0,018	0,034	0,033	0,024	0,012	0,013	0,015
1175	0,000	0,010	0,016	0,006	0,015	0,014	0,030	0,003	0,025	0,020	0,011
1225	0,000	0,014	0,008	0,001	0,038	0,020	0,019	0,024	0,003	0,009	0,013
1275	0,000	0,011	0,004	0,006	0,014	0,006	0,020	0,031	0,008	0,004	0,009
1325	0,000	0,008	0,002	0,001	0,038	0,032	0,023	0,022	0,005	0,012	0,013
1375	0,000	0,012	0,018	0,004	0,046	0,033	0,019	0,026	0,009	0,009	0,011
1425	0,001	0,019	0,012	0,003	0,021	0,032	0,022	0,017	0,015	0,005	0,014
1475	0,001	0,002	0,010	0,003	0,038	0,019	0,005	0,027	0,014	0,016	0,019
1525	0,000	0,009	0,013	0,009	0,030	0,014	0,014	0,026	0,026	0,011	0,018
1575	0,000	0,011	0,012	0,005	0,017	0,022	0,024	0,029	0,018	0,006	0,020
1625	0,001	0,008	0,008	0,007	0,023	0,011	0,014	0,017	0,024	0,019	0,015
1675	0,001	0,002	0,009	0,002	0,032	0,024	0,014	0,041	0,036	0,018	0,033
1725	0,000	0,002	0,016	0,012	0,036	0,017	0,044	0,022	0,026	0,020	0,004
1775	0,001	0,017	0,015	0,007	0,013	0,012	0,018	0,023	0,036	0,009	0,019
1825	0,001	0,073	0,001	0,047	0,118	0,035	0,048	0,030	0,169	0,109	0,055
1875	0,000	0,035	0,005	0,008	0,016	0,014	0,009	0,010	0,046	0,032	0,045
1925	0,000	0,006	0,011	0,006	0,036	0,018	0,037	0,018	0,034	0,036	0,044
1975	0,000	0,003	0,005	0,010	0,034	0,010	0,021	0,017	0,014	0,037	0,013





**E.4 and E.5 Requirements for the test report for power generation units**

**Extract from the test report for unit certification  
„Determination of electrical properties“**

**Nr. BMH-ESH-P200410697-2-R2**

**5.2.5.1 b) Higher frequencies HM-500)**

P/P <sub>n</sub> [%]	5	10	20	30	40	50	60	70	80	90	100
f [kHz]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]	I <sub>h</sub> [%]
2,1	0,006	0,004	0,005	0,019	0,017	0,019	0,009	0,010	0,019	0,046	0,026
2,3	0,008	0,004	0,006	0,021	0,023	0,008	0,007	0,023	0,005	0,018	0,015
2,5	0,007	0,004	0,009	0,003	0,010	0,011	0,004	0,009	0,015	0,012	0,021
2,7	0,007	0,003	0,001	0,011	0,016	0,008	0,010	0,017	0,014	0,008	0,011
2,9	0,012	0,005	0,006	0,013	0,011	0,005	0,017	0,022	0,010	0,010	0,007
3,1	0,004	0,003	0,004	0,006	0,011	0,007	0,008	0,022	0,012	0,007	0,016
3,3	0,004	0,002	0,007	0,021	0,006	0,008	0,021	0,017	0,015	0,004	0,017
3,5	0,002	0,003	0,001	0,013	0,015	0,015	0,017	0,010	0,020	0,036	0,013
3,7	0,015	0,003	0,002	0,008	0,010	0,032	0,035	0,008	0,017	0,062	0,010
3,9	0,009	0,004	0,006	0,017	0,012	0,009	0,014	0,031	0,013	0,060	0,034
4,1	0,002	0,007	0,011	0,036	0,011	0,043	0,021	0,043	0,001	0,089	0,011
4,3	0,010	0,005	0,003	0,024	0,007	0,018	0,013	0,027	0,022	0,069	0,032
4,5	0,029	0,004	0,007	0,049	0,013	0,018	0,012	0,022	0,008	0,067	0,018
4,7	0,035	0,010	0,016	0,098	0,021	0,059	0,013	0,048	0,002	0,041	0,006
4,9	0,023	0,031	0,014	0,360	0,027	0,087	0,026	0,046	0,004	0,026	0,029
5,1	0,023	0,030	0,016	0,184	0,037	0,104	0,035	0,064	0,011	0,060	0,008
5,3	0,032	0,012	0,017	0,078	0,020	0,085	0,010	0,026	0,012	0,068	0,035
5,5	0,032	0,006	0,010	0,069	0,008	0,029	0,017	0,034	0,016	0,065	0,018
5,7	0,010	0,004	0,009	0,042	0,037	0,050	0,007	0,036	0,005	0,041	0,022
5,9	0,008	0,010	0,006	0,020	0,008	0,038	0,014	0,014	0,020	0,052	0,036
6,1	0,011	0,009	0,003	0,019	0,018	0,037	0,007	0,015	0,016	0,058	0,017
6,3	0,013	0,007	0,007	0,027	0,009	0,037	0,021	0,030	0,010	0,078	0,014
6,5	0,008	0,005	0,008	0,030	0,013	0,014	0,008	0,017	0,013	0,068	0,013
6,7	0,005	0,007	0,005	0,023	0,029	0,031	0,019	0,022	0,005	0,055	0,019
6,9	0,010	0,019	0,016	0,006	0,027	0,015	0,009	0,016	0,022	0,046	0,043
7,1	0,015	0,003	0,010	0,020	0,005	0,027	0,031	0,036	0,013	0,037	0,016
7,3	0,020	0,010	0,033	0,033	0,030	0,011	0,011	0,030	0,025	0,035	0,037
7,5	0,009	0,004	0,006	0,028	0,029	0,018	0,007	0,033	0,035	0,011	0,012
7,7	0,019	0,009	0,019	0,007	0,012	0,012	0,012	0,026	0,032	0,042	0,042
7,9	0,018	0,018	0,019	0,021	0,031	0,035	0,002	0,027	0,008	0,032	0,020
8,1	0,028	0,024	0,029	0,055	0,039	0,043	0,039	0,024	0,023	0,031	0,032
8,3	0,039	0,020	0,008	0,033	0,025	0,035	0,036	0,034	0,006	0,039	0,019
8,5	0,034	0,047	0,038	0,033	0,018	0,040	0,032	0,040	0,022	0,004	0,006
8,7	0,044	0,037	0,004	0,034	0,028	0,045	0,022	0,011	0,003	0,022	0,012
8,9	0,037	0,014	0,035	0,020	0,009	0,050	0,031	0,027	0,003	0,028	0,018

Note:

The reference current is 2,17 A.