

# Instruction manual

Little Bee Smart Series Six Bee Eyes+Laser

Thank you for choosing our Six Bee Eyes+Laser,For your personal safety and better use of this product,Please read the manual carefully before using,Follow the procedure, To avoid misuse of personal safety damage and lamp damage.

## 一、 Packing list

After unpacking,Please check the product is qualified,Count all accessories.NO, please contact the distributor!

number	Name	Color	Unit	Quantity
1	Lamps and lanterns	Black	Station	1
2	Power Cord	Black	Ordinance	1
3	Handle	Black	PCS	1
4	Hexagon screws	Black	PCS	2
5	Instructions	Black and white	PCS	1

## 二、 Appearance and LED Function

Switch settings by pressing a button:

\*Click “MENU” Key switch function.

\*Click “UP/DOWN” Switch function or set address code.

\*After switching functions, Click “ENTER” Key save function.



## 三、 Technical parameters

number	Category	Parameter
1	Power supply	AC95V-245V/50Hz
2	Product power	90W (Bee Eyes 72W, 50MW Green Laser)
3	Lamp beads	6 PCS CREE Cree four in one lamp beads, 50mW Green Laser
4	Control	DMX512, 13 channels for international use
5	Mode of operation	DMX512, master/slave, self-walking, voice control
6	Dimming mode	0~100% ultra-smooth dimming
7	Strobe	20 times per second
8	Heat dissipation	Aluminum products cooling, forced cooling fan

#### 四、DMX Channel function:

This product have 13 channels, Specific controls are as follows:

channels	Function	DMX Value	Description
1	X Motor	0-255	0~~255 0-540 degree rotation
2	Y Motor	0-255	0~~255 0-180 degree rotation
3	XY speed	0-255	0~255 from fast to slow
4	Z Motor	0-255	0 ~ 1270-360 degrees rotation, 128-191 forward rotation from slow to fast, 192-255 reverse from fast to slow
5	dimmer	0-255	Linear dimming from dark to light
6	Strobe	0-9	None
		10-255	form slow to fast
7	Red	0-255	Red Dimming from Dark to Light
8	Green	0-255	Green Dimming from Dark to Light
9	Blue	0-255	Blue Dimming from Dark to Light
10	White	0-255	White Dimming from Dark to Light
11	green laser	0-255	green laser Dimming from Dark to Light
12	Macro function	0-50	Channels 1 to 11 are valid
		51-150	auto run
		150-255	voice autorun
13	reset	0-250	none
		251-255	reset after 3 second

Menu: A001-A512 Address Setting A 1-A 9 Self-propelled Mode S1 1-S1 9 Voice Control Mode Number Setting Voice Control Spirit Density Number Setting Voice Control Spirit Density Number Setting Voice Control Spirit Density Effect

#### 五、Other parameters

number	Category	Parameters/details
1	Packaging	Standardized cartons
2	Size of inner box	34*27*24CM
3	Cartons	57*36*52CM
4	N.W	3.15KG
5	G.W	3.80KG
6	Carton weight	16.2KG
7	Power connection	Power Cord
8	Signal connection	Signal input line/output line
9	Material	Product materials: Ferrous, The shell: ABS

#### 六、Maintenance

Do not stare at the luminescent body for a long time, It hurts the eyes;

Clean regularly Lens Keep the brightness and Extension Lamps and lanterns Service life.